



80-929

80-929
LED HID Surge Protector; 100-277V AC; 1.1kV Protection level

Features

- Nominal operating voltage: 100-277V AC
- Maximum discharge current voltage: 320V AC
- Nominal discharge current: 5kA
- Protection level: 1.1kV
- Nominal discharge voltage: 10kA
- Maximum discharge voltage: 20kA
- Frequency: 50-60Hz
- Response time: 25ns
- Outer casing protection grade: IP67
- Operating temperature range: -40°C to 80°C



80-929

For use with Satco Hi-Pro™ LED HID replacement lamps.

Item Number	UPC	Finish	Height	Width	Length	Pack
80-929	045923809293	Black	0.83"	1.42"	3.19"	100



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

