



Search > Results for F28T8/835/ECO > F28T8/835/ECO 109364 F28 T8 3500K 85CRI ECO PROLUME



# F28T8/835/ECO 109364 F28 T8 3500K 85CRI ECO PROLUME

Product Number: 109364  
UPC: 807154193646

**CEE  
Listed**

Log In for Price and Availability

Note: this product is only sold in multiples of 25 items

Specifications	Resources	Technical
<b>Applications</b>		Paint stores, hair salons, retail stores and print shops
<b>Average Life (Hrs)</b>		24000
<b>Base</b>		Medium Bi-Pin
<b>Brand</b>		ProLume Eco-Shield
<b>Bulb</b>		T8
<b>CRI</b>		86
<b>Color Temperature</b>		3500
<b>Cross Reference - Osram Sylvania</b>		FO28/835/XP/SS/ECO
<b>Design Lumens</b>		2660
<b>Dimmable</b>		No
<b>HTS code</b>		8539310070
<b>Initial Lumens</b>		2800
<b>Input Frequency (Hz)</b>		60
<b>Markets</b>		Residential, Commercial
<b>Master Carton Quantity</b>		25
<b>Maximum Overall Diameter</b>		1
<b>Maximum Overall Length</b>		48
<b>Nominal Length</b>		48
<b>Operating Position</b>		Universal
<b>Prod Code</b>		F28T8/835/ECO
<b>Product Category</b>		Linear Fluorescent
<b>Product Description</b>		F28 T8 3500K 85CRI ECO PROLUME
<b>Product Number</b>		109364
<b>Start Type</b>		Instant/Programmed Start
<b>Warranty (Yrs)</b>		2; 3 When Installed with ProLume Ballast
<b>Wattage (W)</b>		28

**Substitute Items:**



F28T8/835/ECO/IC 30155 F28 T8 3500K 86CRI ECO PROLUME

### Products

#### Lamps



#### Ballasts



#### Luminaires



### Resources

- Catalogs
- Sell Sheets
- New Products

### Contact Us

**Corporate Office:**  
Halco Lighting Technologi  
2940 Pacific Drive  
Norcross, GA 30071  
Toll Free: 800.677.3334  
Office: 770.242.3612  
Fax: 800.880.0822  
Email: [customer@hal](mailto:customer@halco.com)



Copyright © 2017 - Halco Lighting Technologies

- [Home](#)
- [News](#)
- [About Us](#)
- [FAQ](#)
- [Site Map](#)
- [Privacy P](#)