

Item #: P305-1-654-L	UPC Code: 844349017387
Product Family Name:	Finish: Chiseled Nickel
Category: Task Lamp	Category Type: Table Lamp
Certification	
Patents	
Notes:	



Image File Name:
P305-1-654-L.jpg



MEASUREMENTS

Width: 7	Length: 7.75	Height: 28.75	Extension: 7
Height Adjustable: Yes	Min Overall Height: 15.00	Max Overall Height: 28.75	Slope: No
Wire Length: 96"	Chain Length:	Safety Cable Included: No	Net Weight: 6.39
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 1	Light Type: Z08,Led			
Max Bulb Wattage: 12	Socket: Led			
Dimmable: Yes	Ballast:	Rated Life Hours: 30000	Photocell Included: N	Lamps Included: Yes
LED Included: Yes	Color Temp.: 3000	CRI: 82	Initial Lumens: 830.300	Delivered Lumens: 705.800



SHIPPING

Carton Width:	Carton Height:	Carton Length:
Carton Weight:	Carton Cubit Feet:	Small Package Shippable: Yes
Master Pack Width: 6.500	Master Pack Height: 9.880	Master Pack Length: 22.000
Master Pack Weight: 15.660	Master Cubic Feet:	Multi-Pack: 2

SHADE / GLASS

Description:	Material: Acrylic
Part No.: P305-CVR	Quantity: 1
Width: 4.75	Height: 0.38
	Length: 4.75

LED

LED

Yes