



Powering Business Worldwide

pe.eaton.com

Definite Purpose Control - Contactor

C25END440A

UPC:782113565309

Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.38 IN
- **Width:** 2.68 IN

Weight:2.3 LB

Notes:Resitive Load rating per pole

Warranties:

- 1 year

Specifications:

- **Connection:** Quick
- **Amperage Rating:** 40A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 25-40A, four-pole
- **Model:** Contactor
- **Number Of Poles:** Four-pole
- **Resistive Load:** 50A
- **Terminals:** Screw/pressure plate and quick connect terminals (side-by-side)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25END440A](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data



