



GE  
Lighting

### 26625 - Integrated 3ft LED Plastic Tubes

#### LED12ET8/3/840

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ LED tubes are ideal for those seeking high energy savings with minimal installation time.
- ☞ Each LED tube is outfitted with an internal GE driver.
- ☞ GE integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.
- ☞ Shatter resistant
- ☞ No UV
- ☞ Easy disposal, non-hazardous waste
- ☞ NSF Rated for food application (shatter resistant)
- ☞ UL Listed

#### Product Photo



#### GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
LED Tube Type	Plastic
10 Digit U	4316826625
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Carton
Estimated Energy Cost per Year	1.45
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	1550 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

#### PRODUCT INFORMATION

Product Code	26625
Description	LED12ET8/3/840
Alternative Unit Of Measure	EACH
Standard Package Quantity	25
Ean UPC	043168266253
Standard Package GTIN	00043168266253
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	25
Sales Unit	Each
UCC	043168266253
Alternative Unit Of Measure	CASE
Standard Package Quantity	25
Ean UPC	043168266253
Standard Package GTIN	10043168266250
No Of Items Per Sales Unit	
No Of Items Per Standard Package	25
Sales Unit	Case
UCC	043168266253

#### DIMENSIONS

Bulb Max Overall Length-MOL	36.0 in
-----------------------------	---------

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	12 W
---------------------	------