

QUOIZEL

Artisans in Lighting...since 1930

Newbury LED

Item #NYL8409K

Product Category: Outdoor Lantern

Finish: Black

Suggested Rooms: Outdoor

Height: 13.50"

Width: 8.00"

Depth: 7.75"

Item Weight: 3.60 lbs

Packed Weight: 5.00 lbs

Dimension Weight: 8 lbs



Description

When it comes to curb appeal outdoor lighting plays a large part in creating a special ambiance. The classic design and beveled glass of the Newbury gives the outside of your home a rich elegance without making it look over embellished. It's a versatile look that coordinates with most any architectural style.

Bulb Type: LED AC 120V Bulb(s) Is Integrated

LED Information

Lumens: 880

Total Watts: 11.0

Color Rendering Index(CRI): 80

Temperature (CCT): 2700

Base Material: BRASS

Listed Mark: ETL Listed

Listed Mark Rated For: Wet

HCWO: 7.000

Canopy/Backplate: 5.500"H x 4.750" W

Wire Length: 6 In

Voltage: 120.000

We reserve the right to revise the design of components of any product due to parts availability or change in our Listed Mark standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product DESIGN that is the SOLE and EXCLUSIVE PROPERTY of Quoizel Lighting Inc. In Compliance with U.S. COPYRIGHT and PATENT requirements, notification is hereby presented in this form that this literature, or the product it depicts, is NOT to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Quoizel Inc. 03/31/2013

Quoizel Inc., 6 Corporate Parkway, Goose Creek SC 29445

www.quoise.com

*distance from wall outlet box to highest point of mounted product

3/27/2017

Quoizel Inc. All Rights Reserved - Designs Protected by Copyright