



Square steel poles drilled for 2 Area Lights at 180°. Designed for ground mounting. Poles are stocked nationwide for quick shipment. Protective packaging ensures poles arrive at the job site good as new.

Color: Bronze

Weight: 433.0 lbs

<b>Project:</b>	<b>Type:</b>
<b>Prepared By:</b>	<b>Date:</b>

Lamp Info		Ballast Info	
Type:	N/A	Type:	N/A
Watts:	0W	120V:	N/A
Shape/Size:	N/A	208V:	N/A
Base:	N/A	240V:	N/A
ANSI:	N/A	277V:	N/A
Hours:	N/A	Input Watts:	0W
Lamp Lumens:	N/A		
Efficacy:	N/A		

### Technical Specifications

**Listings**

**CSA Listed:**

Suitable for wet locations.

**Construction**

**Shaft:**

46,000 p.s.i. minimum yield.

**Hand Holes:**

Reinforced with grounding lug and removable cover.

**Base Plates:**

36,000 p.s.i. minimum yield.

**Shipping Protection:**

All poles are shipped in individual corrugated cartons to prevent finish damage.

**Color:**

Bronze powder coating.

**Height:**

30 FT.

**Gauge:**

7

**Wall Thickness:**

3/16"

**Shaft Size:**

5"

**Hand Hole Dimensions:**

3" x 5"

**Bolt Circle:**

11"

**Base Dimension:**

11"

**Weight:**

433 lbs.

**Anchor Bolt:**

Galvanized anchor bolts and galvanized hardware and anchor bolt template. All bolts have a 3" hook.

**Anchor Bolt Templates:**

WARNING Template must be printed on 11" x 17" sheet for actual size. CHECK SCALE BEFORE USING. Templates shipped with anchor bolts and available .

**Pre-Shipped Anchor Bolts:**

Bolts can be pre-shipped upon request for additional freight charge.

**MaxEPA's/Max Weights:**

70MPH 12.1 ft\_/300 lb  
 80MPH 7.8 ft\_/195 lb  
 90MPH 4.7 ft\_/115 lb  
 100MPH 2.4 ft\_/60 lb  
 110MPH 0.7 ft\_/15 lb.

**Other**

**Terms of Sale:**

Pole Terms of Sale is available .

**Features**

- Designed for ground mounting
- Heavy duty TGIC polyester coating
- Reinforced hand holes with grounding lug and removable cover for easy wiring access
- Anchor Bolt Kit includes pole cap and base cover (sold separately)
- Custom manufactured for each application