

# Outdoor Wall 1Lt RZ

## 49271RZ (Rubbed Bronze)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_



### Ordering Information

Product ID	49271RZ
Finish	Rubbed Bronze

### Dimensions

Extension	9.50"
Height from center of Wall opening	6.50"
Base Backplate	5.50 SQ
Weight	5.50 LBS

### Specifications

Material	Cast Aluminum
Glass Description	Light Amber Etched Seeded

### Electrical

Voltage	120V
---------	------

### Qualifications

Safety Rated	Wet
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

### Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	1
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

### Dimensions

Height	14.00"
Width	8.00"

### Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	23-30W		