



6515503-962: Three Light Pendant



Collection: Jourdanton

UPC #: 785652107542

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 20 5/8"

Height: 8 1/4"

Overall Height: 52 1/4"

Wire: 120" (color/Clear Silver)

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

3 - Medium A19 60w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Brushed Nickel

1 6" Stem - Steel - Brushed Nickel

3 12" Stem - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990P6515503-JOU)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Satin Etched	1	G5600207-619				17				
Shade	Fabric	Faux Silk	1				7 7/8	17 5/8				
Shade	Stainless Steel	Stainless	1				8 1/4	20 5/8				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1			5		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	6515503-962	1	785652107542	23.25	23.25	13.5	4.223	13.3	250	Yes
NJ Pallet		18		48	40	74.5	82.778	239.4		No
NV Pallet		18		48	40	74.5	82.778	239.4		No