



3124505-710: Five Light Chandelier



Collection: Hanford

UPC #:785652110740

Finish: Burnt Sienna (710)

Dimensions:

Diameter: 27 5/8"

Height: 27 5/8"

Weight: 17.1 lbs.

Overall Height: 66 1/8"

Wire: 72" (color/Brown)

Chain: 36"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

5 - Medium A19 100w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Material List:

1 Body - Steel - Burnt Sienna

1 Chain - Steel - Burnt Sienna

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990CH31245_-HAN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	5	G560251-619			5 3/4	5 1/8				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	7/8			5		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	3124505-710	1	785652110740	28.25	27.5	13.25	5.957	22.2	250	Yes
NJ Pallet		9		48	40	75	83.333	198.9		No
NV Pallet		9		48	40	75	83.333	198.9		No