



### 8547991S-71: Small LED Outdoor Wall Lantern



**Collection:** Crowell

**UPC #:** 785652107955

**Finish:** Antique Bronze (71)

### Dimensions:

**Diameter:** 6"      **Extends:** 7 1/2"  
**Height:** 10"      **Wire:** 6" (color/Black/White)  
**Weight:** 2.3 lbs.      **Mounting Proc.:** Cap Nuts  
**Connection:** Mounted To Box  
**Bulb Type:** Modules  
**Bulb Base:** Integrated  
**Volts:** 120  
**Watts:** 9  
**Watts Consumed:** 9  
**Watts Rated:** 9  
**Hours Rated:** 50000  
**Lumens:** 700  
**Bulb Temp:** 2700 °K  
**CRI:** 90

### Features:

- Advanced LED technology that warms in color when dimmed (2700K - 2200K).
- Meets Title 24 energy efficiency standards
- Title 24 compliant high efficacy light source that is not required to be listed in the California Energy Commission Appliance database.

### Material List:

1 Body - Aluminum - Antique Bronze

### Safety Listing:

Safety Listed for Wet Locations

### Instruction Sheets:

Trilingual (English, Spanish, and French) (990W8\_47991\_-CRO)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Creme Parchment	1	G560199-6060			7	3 15/16				

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	4 13/32	4 13/32	3/4		3 1/4	6 3/4

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8547991S-71	1	785652107955	12.5	9.5	8	0.55	3.3	125	Yes
NJ Pallet		135		48	40	77	85.556	446		No

NV Pallet		135		48	40	77	85.556	446		No
-----------	--	-----	--	----	----	----	--------	-----	--	----