



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com



Search within category

LAB500-12-2



Two-hole, aluminum, long barrel, 500 kcmil, 1/2" (12.7mm) stud hole.

BUY NOW

DESIGN / INSTALL

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Product Type	Compression Connectors - Lugs
Material	Tin-Plated Aluminum
CSA Certified	Yes
UL Listed	Yes
Length (In.)	7.36
Length (mm)	186.9
Aluminum or Copper Conductor Size	500 kcmil
Stud Hole Size (In.)	1/2
Stud Hole Spacing (In.)	1.75
Tongue Width (In.)	1.72
Barrel Length (In.)	3.05
Angle	Straight
Conductor Material	Aluminum or Copper
Panduit Color Code	Pink
Panduit Die Index No.	P99
Part Features	dual rated,prefilled joint compound,enclosed barrel,tin plated to inhibit corrosion
Stud Hole Size (mm)	12.7
Stud Hole Spacing (mm)	44.5
Tongue Thickness	0.44
Tongue Thickness (mm)	11.2
Tongue Width (mm)	43.7
Wire Strip Length (In.)	3 1/16
Wire Strip Length (mm)	77.8
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000
Burndy Die Index No.	300
T&B Die Index No.	99

Request a Quote
Are you looking for a free quote on Panduit Products and Solutions?

Yes, I need a quote! ▶

Request a Quote
Are you looking for a free quote on Panduit
Products and Solutions?

Yes, I need a quote! ▶