



GE  
Lighting

### 38958 - Remote 4ft LED Plastic Tubes

#### LED15T8/4/840

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ Each LED tube is operated by a GE Lighttech™ driver.
- ☞ 66% longer life than LFL (50,000 vs. 30,000 hours)
- ☞ Instant on light
- ☞ NSF Rated for food application (shatter resistant)
- ☞ Easy disposal, non-hazardous waste
- ☞ UL Listed
- ☞ DLC Listed

#### Product Photo



#### CAUTIONS & WARNINGS

##### Caution

Risk of Electric Shock

Suitable for damp locations

Not intended for use with emergency exit fixtures or emergency exit lights

#### GENERAL CHARACTERISTICS

Dimmable	Yes
Product Technology	LED
Rated Life (Hours)	50000 h
Dimmable / Non-Dimmable	Yes
LED Tube Type	Plastic
10 Digit U	4316838958
Lamp Count	1
Life in Years	45.7 yr
Requested Structure	Sleeve
Estimated Energy Cost per Year	1.57
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	2050 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

#### PRODUCT INFORMATION

Product Code	38958
Description	LED15T8/4/840
Alternative Unit Of Measure	CASE
Standard Package Quantity	10
Ean UPC	043168389587
Standard Package GTIN	10043168389584
No Of Items Per Sales Unit	
No Of Items Per Standard Package	10
Sales Unit	Case
UCC	043168389587
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168389587
Standard Package GTIN	00043168389587
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168389587

#### DIMENSIONS

Bulb Max Overall Length-MOL	48.0 in
-----------------------------	---------

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	13 W
---------------------	------