



SURECRIMP® ALND ALUM 2 HOLE LONG BARREL



- Manufactured from high strength aluminum alloy which offers maximum conductivity and excellent crimping characteristics.
- Electro-Tin plated for low contact resistance.
- Chamfered entry for easy conductor insertion.
- Color coded end cap identifies the proper compression die.
- Roll marked barrel for easy identification and proper location of crimps.
- Pre-filled with DE-OX prevents oxide from forming.
- Dual rated for Aluminum or Copper conductors.
- UL 486A/B 90° C Listed and CSA Certified.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size applicable when installed with specified dieless tools.
- UL File E6207

| Item ID | Conductor Size | Expanded Conductor | Bolt/Stud Size | Mounting Hole | Mounting Hole | Tang Length | Tang Width | Barrel Length | Strip Length | Overall Length | Color Code | Die Index Number | Die Catalog | Outside Diameter | Inside Diameter | Standard Package | NAED/UP C Number |
|-----------------|----------------|--------------------|----------------|---------------|---------------|-------------|------------|---------------|--------------|----------------|------------|------------------|-------------|------------------|-----------------|------------------|-------------------|
| ALND-6-1 4-1 | 6 AWG | | 1/4 | 0.2810 | 1 | 1.6870 | 0.4490 | 0.6020 | 0.6645 | 2.6500 | GRAY | 346 | ILD-346 | 0.3380 | 0.1940 | 20 | 07836696 90842 |