



Search within category

BUY NOW

DESIGN / INSTALL



LAMA1000-58-6Y

One-hole, aluminum, single barrel lug, type LAMA, 500 - 1000 kcmil, 5/8" (15.9mm) stud hole. LAMA1000-58-6Y replaces LAMA1000-58-6

Specs Packaging Details Documents [★ Add to Favorites](#) [Add to BOM](#)

Note	LAMA1000-58-6Y replaces LAMA1000-58-6
Material	Tin-Plated Aluminum
Copper and Aluminum Conductor Size Range	500 kcmil - 1000 kcmil
No. of Ports	—
Stud Hole Size In. (mm)	5/8 (15.875)
Stud Hole Spacing In. (mm)	—
Height 1 In. (mm)	—
Height 2 In. (mm)	—
Height In (mm)	1.94 (54.1)
Hex Key Size (In.)	3/8
Length In (mm)	3.50 (88.9)
Mounting Hole Spacing In. (mm)	—
NEMA Hole Spacing	—
Tongue Length In. (mm)	1.88 (44.5)
Tongue Thickness In. (mm)	0.50 (12.7)
Tongue Width In. (mm)	1.75 (44.45)
Width In (mm)	—
CSA Certified	—
Max. Voltage Rating	600V
Temperature Rating	—
Tin-Plating Meets ASTM B545-97, Class C	320µ in (8µ m)
UL Listed	—
UL Temperature Rating	90°C
UL and CSA Temperature Rating	—
UL and CSA Voltage Rating	—
Insulation	—

Request a Quote  
Are you looking for a free quote on Panduit Products and Solutions?

**Yes, I need a quote! ▶**

Part Number Series	LAMA
BMEcat - Halogen Free	true
Part Features	The use of Panduit oxide inhibiting joint compound (CMP-100) is recommended for pad to pad and conductor connections
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

---

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)

Request a Quote  
Are you looking for a free quote on Panduit  
Products and Solutions?

---

**Yes, I need a quote!** ▶