

MINKA-LAVERY®

Item #: 3295-613	UPC Code: 747396097374
Product Family Name: Audrey's Point	Finish: Polished Nickel
Category: Chandeliers	Category Type: Chandelier
Certification 3057374	
Patents	
Notes:	



Image File Name:

3295-613--
1475632808.jpg



MEASUREMENTS

Width: 25	Length: 25	Height: 25.25	Extension:
Height Adjustable: Yes	Min Overall Height: 29.25	Max Overall Height: 99.75	Slope: Yes
Wire Length: 120"	Chain Length: 72"	Safety Cable Included: No	Net Weight: 12.63
Canopy Width: 5.13	Canopy Height: 1.00	Canopy Length: 5.13	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 5	Light Type: A-19,Med			
Max Bulb Wattage: 100	Socket: E26,Medium			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G3291	Quantity: 5
Width: 5.25	Height: 5.50
	Length: 5.25



SHIPPING

Carton Width: 13.750	Carton Height: 25.500	Carton Length: 23.750
Carton Weight: 19.514	Carton Cubic Feet: 4.819	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



ETL Intertek

Yes