

MINKA-LAVERY®

Item #: 3336-84	UPC Code: 747396096902
Product Family Name: Savannah Row	Finish: Brushed Nickel
Category: Chandeliers	Category Type: Chandelier
Certification E314733	
Patents	
Notes:	



Image File Name:

3336-84--
1475632808.jpg



MEASUREMENTS

Width: 26	Length: 26	Height: 26.75	Extension: 26
Height Adjustable: Yes	Min Overall Height: 30.00	Max Overall Height: 102.00	Slope: Yes
Wire Length: 120"	Chain Length: 72"	Safety Cable Included: No	Net Weight: 8.14
Canopy Width: 5.00	Canopy Height: 1.00	Canopy Length: 5.00	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 6	Light Type: B10.5,Cand			
Max Bulb Wattage: 60	Socket: E12,Candelabra			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description: GLASS BALL	Material: Glass
Part No.:	Quantity: 1
Width: 2.36	Height: 1.42
	Length: 2.36



SHIPPING

Carton Width: 13.250	Carton Height: 27.750	Carton Length: 29.500
Carton Weight: 14.850	Carton Cubic Feet: 6.277	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



UL Listed

Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties

Rev 12.31.2015