

MINKA-LAVERY®

Item #: 72543-593	UPC Code: 747396097954
Product Family Name: Astrapia II	Finish: Dark Rubbed Sienna
Category: Wall Mount	Category Type: Outdoor Lighting
Certification 3159126	
Patents	
Notes:	



Image File Name:
72543-593--
1457686923.jpg



MEASUREMENTS

Width: 11	Length: 13.5	Height: 28.25	Extension: 13.5
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7"	Chain Length:	Safety Cable Included: No	Net Weight: 12.70
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width: 5.00	Backplate Height: 9.00	Center to Top: 13.25	Center to Bottom: 15.00

SHADE / GLASS

Description:	Material: Glass
Part No.: G72543	Quantity: 4
Width: 6.00	Height: 9.00
	Length: 7.75

LAMPING

No. of Bulbs: 4	Light Type: B10.5,Cand			
Max Bulb Wattage: 60	Socket: E12,Candelabra			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:



SHIPPING

Carton Width: 14.500	Carton Height: 31.500	Carton Length: 16.500	
Carton Weight: 17.250	Carton Cubit Feet: 4.361	Small Package Shippable: Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack: 1



Wet Location

Yes



ETL Intertek

Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties