

MINKA-LAVERY®

Item #: 72546-593	UPC Code: 747396097978
Product Family Name: Astrapia II	Finish: Dark Rubbed Sienna
Category: Post Mount Lantern	Category Type: Outdoor Lighting
Certification 3195126	
Patents	
Notes:	



Image File Name:
72546-593--
1456784640.jpg



MEASUREMENTS

Width: 11	Length: 11	Height: 21	Extension: No
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 9.88
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 4	Light Type: B10.5 Cand			
Max Bulb Wattage: 60	Socket: E12, Cand			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G72543	Quantity: 4
Width: 6.00	Height: 9.00
	Length: 7.75



SHIPPING

Carton Width: 14.500	Carton Height: 24.000	Carton Length: 14.500
Carton Weight: 13.420	Carton Cubit Feet: 2.920	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



Wet Location

Yes



ETL Intertek

Yes