



# S9331

13.5W/LED/7"FLUSH/30K/RD/WH  
 13.5 watt; 7" Flush Mount LED Fixture; 3000K; Round Shape;  
 White Finish; 120 volts

### Features

- Surface mount fixture
- Solid State LED lighting
- Long life
- 5 Year limited warranty
- Dimmable
- Damp location



S9331

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Fixture Type	Base
S9331	BLINK	045923093319	120	13.5	60W	Flush Mount	Connector

  

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
13.5W/LED/7"FLUSH/30K/RD/WH	Dimmable	<a href="#">Compatible dimmers for S9331</a>	White	1"	7.00"	820	40000

  

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3000	Warm White	80+	108	-18C (0F) to a maximum of +46C (+115F)	12	Box	ENERGY STAR

  

Material	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Housing: Die cast aluminum	Yes	Yes	cETLus - Damp Location Rated	<a href="#">5 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

