

Job Name:		Item Number:	
Specifier Name:		Sales Agency:	
Specifier Contact:		Agency Contact:	
Fixture Type:		Comments:	
Quantity:		Approval:	

**10w 24V Frosted T3 Festoon Xenon**



D: 3/8" L: 2" H: 1 11/16"

**Description**

Ambiance Lx Xenon Festoons revolutionized the under cabinet lighting industry and continue to be an industry standard. They are available in 5, 7 and 10 watts and 12 or 24V. Choose from a wide beam or directional lampholder to easily position light where you need it (lampholder sold separately).

**Specifications**

Item Number	97121-33
Dimensions	D: 3/8" L: 2" H: 1 11/16"
Min. Spacing	2" on center
Voltage	24V
Lamp Type	T3
Lamp Base	Festoon
Light Source	Xenon
Color Temperature	2650°K
Lumens	83
Watts Consumed	8.4 watts
Watts Rated	10 watts
Efficacy	9.9 lm/w
Color Rendering	>90 CRI
Rated Average Life	12,000 hours
Lamp Appearance	Frosted lens to reduce glare
Warranty	1-Year Warranty


**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	97121-33	1	785652009723	1.5	0.5	0.5	0	0.006	Yes
Master Pack		2500	10785652009720	12.63	10.38	9.63	0.731	15	Yes
Shipping Master		5000	20785652009727	20.75	11.75	13.75	1.94	30	Yes

**Photometric Diagram:**

Lamp Item #	Lampholder Spacing	Distance to Illuminated Surface				
		6"	12"	18"	24"	30"
97118(-xx) (5w, 12V)	2"	114	52	24	14	10
	4"	71	32	15	8.9	6.4
	6"	64	29	13	8	5.7
97120(-xx) (5w, 24V)	8"	57	26	12	7.1	5.1
	10"	51	23	11	6.3	4.5
	12"	45	20	9.5	5.6	4.0
97119(-xx) (10w, 12V)	4"	179	81	38	22	16
	6"	160	72	34	20	14
	8"	142	64	30	18	13
97121(-xx) (10w, 24V)	10"	128	58	27	16	11
	12"	114	52	24	14	10

**Component Diagram:**



**AMBIANCE**  
Lighting Systems

7400 Linder Ave. | Skokie, Illinois 60077 | 800-347-5483  
© 2013 Sea Gull Lighting LLC, a Generation Brands Company.