



GE
Lighting

35789 - Integrated 3ft LED Glass Tubes

LED11ET8/G/3/850

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ Each LED tube is outfitted with an internal GE driver.
- ☞ The GE integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.
- ☞ 66% longer life than LFL (50,000 vs. 30,000 hours)
- ☞ No UV
- ☞ Easy disposal, non-hazardous waste
- ☞ Check ballast compatibility at www.gelighting.com/LEDTUBES-ballast-compatibility
- ☞ UL Listed

Product Photo



GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
LED Tube Type	Glass
10 Digit U	4316835789
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Sleeve
Estimated Energy Cost per Year	1.39
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	1600 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	35789
Description	LED11ET8/G/3/850
Alternative Unit Of Measure	CASE
Standard Package Quantity	20
Ean UPC	043168357890
Standard Package GTIN	10043168357897
No Of Items Per Sales Unit	
No Of Items Per Standard Package	20
Sales Unit	Case
UCC	043168357890
Alternative Unit Of Measure	EACH
Standard Package Quantity	20
Ean UPC	043168357890
Standard Package GTIN	00043168357890
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
Sales Unit	Each
UCC	043168357890

DIMENSIONS

Bulb Max Overall Length-MOL	36.0 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	11 W
---------------------	------