



A-Shape LED

17A21/END/2700 DIM 6/1

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data

• General Characteristics

| | |
|-------------------------|----------|
| Cap-Base | E26 |
| Bulb | A21 |
| Rated Avg. Life (Hours) | 25000 hr |

• Light Technical Characteristics

| | |
|------------------------------|--------------------|
| Color Code | WW |
| Color Designation | Warm White |
| Correlated Color Temperature | 2700 K |
| CRI | 80 |
| Color Temp. (Kelvin) | 2700 K [CCT 2700K] |
| Rated Luminous Flux | 1100 Lm |

• Electrical Characteristics

| | |
|-------------------|--------|
| Wattage | 17 W |
| Wattage Technical | 17.0 W |
| Voltage | 120 V |
| Power Factor | 0.71 - |
| Lamp Current mA | 195 mA |
| Dimmable | Yes |

• Environmental characteristics

| | |
|-------------------------------|---|
| Energy Efficiency Label (EEL) | A |
|-------------------------------|---|

• Product Dimensions

| | |
|-------------------------|----------------|
| Overall Length C [inch] | 5.039 (max) in |
|-------------------------|----------------|

• Product Data

| | |
|--------------------|-----------------------------|
| Product number | 418590 |
| Full product name | 17A21/END/2700 DIM 6/1 |
| Short product name | 17A21/END/2700-1100 DIM 6/1 |
| Pieces per Sku | 1 |
| eop_pck_cfg | 6 |
| Skus/Case | 6 |
| Bar code on pack | 46677418595 |
| Bar code on case | 50046677418590 |
| Logistics code(s) | 929000201804 |
| eop_net_weight_pp | 0.224 kg |



PHILIPS

sense and simplicity