



Lamps

Ballasts

Luminaires

Company

Customer Care

Contact Us

LAMP RECALL

Search

Search > Results for 80882 > T8FR17/850/DIR/LED 80882 LED T8 17W 5000K Ballast Compatible Direct Replacement Dimmable G13 ProLED



T8FR17/850/DIR/LED 80882 LED T8 17W 5000K Ballast Compatible Direct Replacement Dimmable G13 ProLED

Product Number: 80882
UPC: 807154808823

[Log In for Price and Availability](#)

Note: this product is only sold in multiples of 25 items

Specifications	Resources	Technical
Applications	Hospitality, Retail, Food Service, Office, Medical, Education	
Average Life (Hrs)	50000	
Base	Medium Bi Pin	
Beam Spread	270	
Brand	ProLED	
Bulb	T8	
CRI	82	
Color Temperature	5000	
Dimmable	Yes	
ENERGY STAR	No	
Equivalent Wattage	32	
Finish	Frosted	
Initial Lumens	1800	
Inner Carton Quantity	1	
Input Frequency (Hz)	60	
Markets	Residential, Commercial	
Master Carton Quantity	25	
Maximum Overall Diameter	1	
Maximum Overall Length	48	
Nominal Length	48	
Operating Position	Universal	
Product Category	LED	
Product Description	LED T8 17W 5000K Direct Replacement Dimmable G13 ProLED	
Product Number	80882	
Start Type	Instant Start	
Voltage (V)	120-277	
Warranty (Yrs)	5	
Wattage (W)	17	

Top

Products

Lamps



Ballasts



Luminaires



Resources

Catalog
ProLED Brochure
New Products (PDF)
New Products (XLS)

ProLED Panel Light
ProLED Volumetric
ProLED Downlight
Retrofit

Contact Us

Corporate Office:
Halco Lighting Technologies
2940 Pacific Drive
Norcross, GA 30071
Toll Free: 800.677.3334
Office: 770.242.3612
Fax: 800.880.0822



Copyright © 2016 - Halco Lighting Technologies

[Home](#) [News](#) [About Us](#) [FAQ](#) [Site Map](#) [Privacy Policy](#)