



T&B Catalog Number:

S500WHE-RL

UPC Number:

04226900563

Status:

Active

Description:

White Lamp holder, material-Die Cast Zinc Zamak 3. Lamp maximum-150 watt, PAR 38 or R40. Inside gasket and ground screw included.

Features

- Clean lines and precision manufacturing result in a fixture which will enhance any application
- High quality replaceable porcelain socket with high-temperature leads allow for easy field maintenance
- Positive locking mounting arm keeps fixture in aimed position to reduce costly call-backs and ground screw boss in arm

Application

- Low maintenance indoor/outdoor lighting where moisture, dirt, dust, corrosion and rough service are problems
- To light cold storage facilities, walkways, bridges, tunnels and security locations
- Used with colored globes as warning, caution or directional lights

General

Material	Die Cast Zinc
Color	White
Maximum Wattage	150

Packaging

T&B Order Multiple	20
Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	0.27 lbs. Each

Application Support

US Cutsheet PDF Catalog Link	Available on Website
------------------------------	----------------------

Notes

Suitable for use in wet locations

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com