



GE
Lighting

35196 - GE LED MRX16

LED7XDMRX1683035

Product Photo



GENERAL CHARACTERISTICS

Base Description	GU5.4
Base Type	Plug-in
Dimmable	Yes
Product Color	White
Product Technology	LED
Rated Life (Hours)	25000 h
Dimmable / Non-Dimmable	Yes
Base	GU5.5
Bulb Shape	MR16

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	1350 cd
Lumens per Watt (Efficacy)	71 lm
Nominal Initial Lumen per Watt	71
Rated Beam Spread	35 deg
Initial Lumens-nominal	500 lm
Color Rendering Index-CRI	80
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	35196
Description	LED7XDMRX1683035
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168351966
Standard Package GTIN	10043168351963
No Of Items Per Sales Unit	
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	043168351966
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168351966
Standard Package GTIN	00043168351966
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168351966

DIMENSIONS

Bulb Max Overall Length-MOL	2.2 mm
-----------------------------	--------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	12 V
Input Voltage [nom]	12 V
Rated power (Watts)	7 W