



Job Name:

Job Type:

Comments:

Quantity:

### 96119S-33: Lx LED Frosted Festoon Lamp - 4000K 12v Dimensions:



**Bulb Appearance:**

**Gas Filled:**

**Bulb Base:** festoon

**Volts:** 12

**Watts:** 0.6

**Watts Consumed:** 0.648

**Watts Rated:** 0.6

**Hours Rated:** 35000

**Bulb Temp:** 4000 °K

**CRI:** 85

#### Features:

- The advanced LED technology in Sea Gull Lighting products helps to protect our environment. Not only by using less energy, but by reducing the amount of mercury and hazardous materials that end up in our Earth's land-fills.

**Collections:** Ambiance® Lx LED Festoon (Primary)  
Ambiance® LED Under Cabinet

It's a snap to upgrade existing xenon linear systems to energy saving, money saving lighting. No need to replace or re-invest in your entire system. The LED festoon is an opportunity to retrofit or replace traditional under-the-counter systems and fills the need to provide "green" lighting solutions.

Applications: Task & accent lighting for undercabinet, coves, toe-kick spaces and so much more. Directional nature of LED is ideal for in-cabinet lighting.

Retrofit/Remodel Installations for Magnetic Transformer Systems - JUST REPLACE THE LAMP!

Compatible as a retrofit for existing Lx xenon lamp and compatible xenon lamp systems.

Note: The unique design of the PCB (Printed Circuit Board) makes over voltage due to under capacity a non-issue.

Retrofit/Remodel Installations for Electronic Transformer Systemsz  
60w zero-load LED driver available for replacing electronic transformers due to minimum load requirement. Available drivers: 96223S-12 & 96223S-15.

Product Features: Ease of installation. Ease of retrofit/remodel. Bendable/flexibility of the system.

Dimmability: Dimmable with standard incandescent dimming switch.

A "Fit & Forget" Solution: Offering 35,000 hours of useful life (equivalent to 30 years at 20 hours of use per week)

Efficacy Cool White: 45 Lumens/Watt

Color Rendering: 4000K - CRI 85+

#### Material List:

#### Safety Listing:

ETL Listed for Damp Locations  
cETL Listed for Damp Locations

#### Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1715FS)

LED Festoon Product Line Options & Features:

- 12v and 24v
- Warm (3000K)
- Cool (4000K)
- Clear lens for optimal performance
- Frosted lens to reduce glare
- Color-coded PCB to visually distinguish between warm and cool color temperature LED festoons
- Color-coded end-caps to identify 12v (white) and 24v (black)
- 3 Year Warranty

UPC #:785652028076

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	96119S-33	1	785652028076	2	2	0.75	0.002	0.001	Yes
Master Pack	96119S-33	10	10785652028073	9.25	2.38	1.18	0.015	0.2	Yes
NJ Pallet		25000		48	40	72	80	635	No
NV Pallet		25000		48	40	72	80	635	No