



Riser-Gard Flexible Raceway

T&B Catalog Number:

DG4X1C-1600

UPC Number:

79120721713

Status:

Active

Description:

1-1/4 Inch Riser-Gard orange corrugated non-metallic flexible raceway with tape, reel length-1600 foot.

Features

UL Listed and is available with tape pre-installed.
Listed to UL 2024 in accordance with the National Electrical Code per Articles 725, 770, 800 and 820 for Riser, General Purpose and other cabling optical fiber/telecommunication applications.

Application

Riser-Gard is suitable for use in vertical runs in a shaft or between floors, as well as areas other than the plenum.

Riser and general purpose applications

General

Material	Non-Metallic
Color	Orange
Reel Length (feet)	1600
Reel Type	Wood
Reel Size (Feet x Width)	48" x 46"
Storage Temperatures	-4 degree F to 158 degree F
Handling Temperatures	-4 degree to 104 degree F
Pull Tape (lbs)	900

Dimension Information

Size (inches)	1 1/4
Minimum Bend Radius (inches)	8
Minimum O.D. (inches)	1.64
Maximum O. D. (inches)	1.69

Packaging

T&B Order Multiple	1600
Package in Units	1600
T&B Sold in UOM	Feet
T&B Weight Per UOM	21.63 lbs. per 100

Application Support

T&B Sales Drawings	wsd-ac04182
--------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
e151168

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com