



# Catamount®

Heavy-Duty

T&B Catalog Number:

L-8-120-9-C

UPC Number:

72849491750

Status:

Active

Description:

Heavy Duty Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 200mm (7.87 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.6mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

## General

Material	Nylon 6.6
Color	Natural

## Dimension Information

Nominal Length (inches)	8
Length (inches)	8.0
Width (inches)	0.300
Max. Wire Bundle Diameter (inches)	2
Min. Wire Bundle Diameter (inches)	3/16

## Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

## Tooling

Application Tools	ERG120
-------------------	--------

## Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	7.5 lbs. per 1000

## Application Support

T&B Sales Drawings	wsd-000223
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

## Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com