

LOGO! TD TEXTDISPLAY, FOR LOGO! ..0BA6 AND ..0BA7, 4 LINES, WITH CABLE (2.5M) AND MOUNTING ACCESSORIES, CONFIGURATION WITH LOGO! SOFT COMFORT V6.0



General information

Suitability for use	Connection to all LOGO! basic units from ..0BA6
---------------------	---

Display

Design of display	STN
-------------------	-----

Line display

- | | |
|---|----|
| <ul style="list-style-type: none"> • Number of lines | 4 |
| <ul style="list-style-type: none"> • Number of characters per line | 24 |

Backlighting

- | | |
|--|-----|
| <ul style="list-style-type: none"> • Type of backlighting | LED |
|--|-----|

Control elements

Keyboard fonts

- | | |
|--|-----|
| <ul style="list-style-type: none"> • System keys | Yes |
| <ul style="list-style-type: none"> — Number of configurable system keys | 10 |
| <ul style="list-style-type: none"> • Numeric/alphabetical input | No |
| <ul style="list-style-type: none"> — alphanumeric keyboard | |

Supply voltage

Type of supply voltage	AC/DC
------------------------	-------

Interfaces	
Number of RS 485 interfaces	0
Degree and class of protection	
IP (at the front)	IP40
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Accessories	
Function description	Connecting cable length 2.5 m
belongs to product	LOGO!
Dimensions	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Overall depth	38.7 mm
Weights	
Weight, approx.	220 g
Scope of supply	
Delivery quantity in pieces	1
last modified:	03/24/2017