

SIMATIC S7-300, ANALOG OUTPUT SM 332, OPTICALLY ISOLATED, 4 AO, U/I; DIAGNOSTICS; RESOLUTION 11/12 BITS, 20 PIN, REMOVE/INSERT W. ACTIVE, BACKPLANE BUS



Figure similar

Supply voltage	
Load voltage L+	
• Rated value (DC)	24 V
• Reverse polarity protection	Yes
Input current	
from load voltage L+ (without load), max.	240 mA
from backplane bus 5 V DC, max.	60 mA
Power loss	
Power loss, typ.	3 W
Analog outputs	
Number of analog outputs	4
Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	25 mA
Current output, no-load voltage, max.	18 V
Output ranges, voltage	
• 0 to 10 V	Yes

• 1 V to 5 V	Yes
• -10 V to +10 V	Yes
Output ranges, current	
• 0 to 20 mA	Yes
• -20 mA to +20 mA	Yes
• 4 mA to 20 mA	Yes
Load impedance (in rated range of output)	
• with voltage outputs, min.	1 k Ω
• with voltage outputs, capacitive load, max.	1 μ F
• with current outputs, max.	500 Ω
• with current outputs, inductive load, max.	10 mH
Cable length	
• shielded, max.	200 m
Analog value generation for the outputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	12 bit; \pm 10 V, \pm 20 mA, 4 mA to 20 mA, 1 V to 5 V: 11 bit + sign; 0 V to 10 V, 0 mA to 20 mA: 12 bit
• Conversion time (per channel)	0.8 ms
Settling time	
• for resistive load	0.2 ms
• for capacitive load	3.3 ms
• for inductive load	0.5 ms; 0.5 ms (1 mH); 3.3 ms (10 mH)
Errors/accuracies	
Operational error limit in overall temperature range	
• Voltage, relative to output range, (+/-)	0.5 %
• Current, relative to output range, (+/-)	0.6 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to output range, (+/-)	0.4 %
• Current, relative to output range, (+/-)	0.5 %
Interrupts/diagnostics/status information	
Diagnostic functions	Yes; Parameterizable
Substitute values connectable	Yes; Parameterizable
Alarms	
• Diagnostic alarm	Yes; Parameterizable
Diagnostic messages	
• Diagnostic information readable	Yes
Diagnostics indication LED	
• Group error SF (red)	Yes
Potential separation	
Potential separation analog outputs	

• between the channels and backplane bus

Yes

Isolation

Isolation tested with

500 V DC

Connection method

required front connector

20-pin

Dimensions

Width

40 mm

Height

125 mm

Depth

117 mm

Weights

Weight, approx.

220 g

last modified:

03/24/2017