



Hoffman

Hinge-Cover with 3-Point Latch or Quick-Release Latches, Type 4X

Catalog Number: A36H3012GQRLP
US List Price (USD): \$1,697.00

Bulletin Number:

- A17W3
- A17WM

Material:

- Fiberglass



Model Code:

- 22660

Ship Wt. Std. Pkg. (lbs):

- 54.0

Interchangeable:

- False

IP Rating:

- IP66

Industry Standards:

UL 508A Listed; Type 3, 3R, 4, 4X, 12, 13; File No. E61997 cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12, 13; File No. E61997 Enclosure flammability evaluated per UL 508A NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13 IEC 60529, IP66 Meets NEMA Type 3RX requirements

Description

A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or Hoffman's exclusive POWERGLIDE™ Handle with 3-point latching, for ease of access with increased security.

Applications:

A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or Hoffman's exclusive POWERGLIDE™ Handle with 3-point latching, for ease of access with increased security.

Specifications:

- Fiberglass-reinforced material has excellent temperature and chemical resistance qualities and exhibits outstanding physical properties
- Type 316L stainless steel padlocking POWERGLIDE Handle on 3-point latch versions assures security and a water-tight seal while still allowing convenient access
- Quick-release latch versions feature fiberglass-reinforced polyester latches with integral Type 316L stainless steel padlocking hasp
- Seams are sealed; no holes or knockouts
- Gasket assures water-tight and dust-tight seal
- Fiberglass material is easily punched, drilled, filed or sawed
- Data pocket is high-impact thermoplastic
- Copper-flashed steel collar studs for mounting optional panels and terminal block kits

Finish:

Fiberglass enclosure is gray inside and out. Handle is Type 316L stainless steel electropolished. Optional steel panels are painted white. Optional stainless steel, aluminum and composite panels available in select sizes.

Accessories:

- H2OMIT™ Thermoelectric Dehumidifier
- H2OMIT™ Vent Drains, Type 4X
- HOL-SEALERS™ Non-Metallic Hole Seals

- Panels
- Stainless Steel Window Kits
- Terminal Block Kit Assembly
- Thermal Accessories

Modifications and Customizations:

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

Notes:

Purchase panels separately. Optional stainless steel, composite and aluminum panels available for most sizes. See General Accessories

Technical Data

Hinge-Cover with 3-Point Latch or Quick-Release Latches, Type 4X


Catalog Number	A36H3012GQRLP
A in.	36.25
B in.	30.25
C in.	12
Description	Quick-Release Latch
Panel Size in.	33.00 x 27.00
Conductive Panel	A36P30G
Panel	A36P30
No. of latches	5
G x H in.	37.58 x 24.00

Certifications

 EU Certification

 UL Certification

Documents

 Spec Sheet

 DOC


 3D STEP CAD

 2D DXF CAD




 Instruction Manual

 Instruction Manual

 Dimension Drawing

 Dimension Drawing

Accessories

Item		
	PANELITE LED Enclosure Light	LED24V15
	HOL-SEALERS Non-Metallic Hole Seals	ASPB05075NM
	24V w/ SS shroud	TE162024011