

LET-151 Transformer



FEATURES



- Electronic transformer
- UL and C-UL recognized
- 5.9oz. (167g)
- 35°C maximum ambient temperature
- 90°C maximum case temperature
- 120V, 50/60Hz input @ 1.25A
- 11.75Vac, 30kHz output @ 12.56A
- 150W maximum load
- 50W minimum load with or without dimming
- 0.985 power factor
- Maximum THD 14.8%
- Waterproofing potting
- Auto-reset electronic short circuit, overload protection and thermal cut-off @ 125°C with the fuse on primary.




LET-151-Specs • Subject to change without notice • Rev 2016.12.16 • 1/3

Features


DIMENSIONS



OUTPUT VOLTAGE VS. LOAD @ 120V



OUTPUT VOLTAGE VS. INPUT @ MAX LOAD



LET-151 Transformer

Project

Type

Notes

Product Code

1 **2**

1. Transformer

LET-151

2. Voltage

120