



<b>F32T8/850/ES-28W</b>	
<b>Std. Pack Qty.</b>	<b>25</b>
<b>Order Code</b>	

PRODUCT SPECIFICATION

FLUORESCENT LAMPS



**GENERAL CHARACTERISTICS**

<b>Lamp Type</b>	<b>Linear</b>
<b>Bulb</b>	<b>T8</b>
<b>Base</b>	<b>G13</b>
<b>Watts</b>	<b>28</b>
<b>Rated Avg. Life (hrs)</b>	
3 hours per start	30000
12 hours per start	36000

**DIMENSIONS**

<b>Norminal Overall Length (inches) (C)</b>	<b>47.77</b>
<b>Norminal Bulb Diameter (inches) (D)</b>	<b>1.02</b>
<b>Face to End of Opposing End (inches)</b>	
Max. (B)	47.50
Min. (B)	47.41

**Spectral Power Distribution**



**PHOTOMETRIC CHARACTERISTICS**

<b>Initial Lumens</b>	<b>2725</b>
<b>Mean Lumens</b>	<b>2560</b>
<b>Color Temperature</b>	<b>5000 K</b>
<b>Color Rendering Index (CRI)</b>	<b>85</b>


**ELECTRICAL CHARACTERISTICS**

<b>Min. Starting Temperature (C)</b>	<b>10</b>
<b>Min. Cathode Resistance Ratio (Rh/Rc)</b>	<b>4.25</b>
<b>Max. Cathode Resistance Ratio (Rh/Rc)</b>	<b>6.5</b>
<b>Max. Current Crest Factor</b>	<b>1.7</b>

**Features**

- 

**Lamp Mortality**



**Lumen Maintenance**

