






## 85 01 250 KNIPEX SmartGrip®

Water Pump Pliers with automatic adjustment

PATENTED



- Technical details
- Description
- Special
- Applications
- PDF

	<b>No.</b>	85 01 250
	<b>EAN</b>	4003773061304
	<b>Pliers</b>	grey atramentized
	<b>Head</b>	polished
	<b>Handles</b>	with non-slip plastic coating
	<b>Capacities for pipes</b>	1 1/4 Ø Inch
	<b>Capacities for pipes</b>	32 Ø mm
	<b>Capacities for nuts</b>	36 mm
	<b>Length</b>	250 mm
	<b>Net weight</b>	370 g

- ideal for frequent changeovers to workpieces of different sizes
- automatic adjustment per one-hand operation both for right-handed and left-handed use
- good access to the workpiece thanks to the slim dimensions of head and joint area and flush joint bolt
- self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- box-joint design for high stability due to double guide
- guard prevents operators' fingers being pinched
- locking lever for space saving transport with reliable closed handles
- Chrome vanadium electric steel, forged, oil-hardened

Adjustment to suit the workpiece is automatic with the KNIPEX SmartGrip®! Place the outer jaw on the workpiece, squeeze the handles - turn!



Automatic adjustment: no time-consuming trial and error-adjusting to find the correct opening size in case of differently sized workpieces (e.g. the red highlighted nuts and fittings). Everything done with a single grasp.



Locking lever for space saving transport with reliable closed handles



Slim dimensions for good access to the workpiece using one-hand operation



Self-locking on pipes and nuts: no slipping on the workpiece



Product Information KNIPEX SmartGrip® 85 01 250  
technical change and errors excepted