

95 32 320

Cable Cutter (ratchet principle, 3-stage)



- Sturdy. Easy to use. Stable.
- Innovative ratchet-drive.
- For cable up to 60 mm diameter.
- easy handling due to low weight (825 g) and compact construction (320 mm length) - also usable in confined areas
- cutting through copper and aluminium cables with diameters of up to 60 mm in one-hand and two-hand operation
- hardened cutting edges, precisely ground, cut smoothly and neatly without crushing
- for cutting copper and aluminium single conductors as well as multiple stranded cables (not suitable for steel wire and wire ropes)
- innovative three-stage ratchet-drive with high leverage for easy cutting in one-hand and two-hand operation
- fixed handle with support area for putting down the pliers when cutting
- High-grade special tool steel, forged, oil-hardened

First manual ratchet-action cable cutter for one-hand and two-hand operation for cutting copper and aluminium cables with diameters of up to 60 mm!

Article No.	95 32 320
EAN	4003773075172
Tool	black atramentized
Handles	with multi-component grips
Head	polished
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	60
Cutting capacity copper cable, multiple-stranded mm²	600
MCM	1200
Length mm	320
Length mm	320
Net weight g	825



technical change and errors excepted



Spare Parts

Article No.	EAN	
95 39 320 01	4003773075714	Pivot cutter repair kit for 95 32 320 and 95 36 320
95 39 320 02	4003773075721	Fixed cutter repair kit for 95 32 320 and 95 36 320