



S1927

LU200/ET18
200 watt; High Pressure Sodium HID; Mogul base; ET18; Clear;
22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1927

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S1927	045923019272	200	ET18	Mogul	E39	S66	LU200/ET18
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	9.65"	2-1/4"	24000	22000	2100	12	22
Burning Position			Hg Content	RoHS Compliant			
Universal			20.0 mg	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

