



*Hoffman*

## Flat Cover with Screws, Type 4X

Catalog Number: HJ1008HWLG  
US List Price (USD): \$92.07

### Bulletin Number:

- HJ

### Material:

- Fiberglass



### Model Code:

- 15877

### Ship Wt. Std. Pkg. (lbs):

- 5.0

### Interchangeable:

- False

### Industry Standards:

UL 508A Listed; Type 3, 3R, 4, 4X, 12, 13; File No. E54315 cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12, 13; File No. E54315 Enclosure flammability per UL 508A NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13 CSA File No. 217184: Type 3, 3R, 4, 4X, 12, 13 IEC 60529, IP66 *Meets NEMA Type 3RX requirements*

## Description

---

Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with removable and hinged covers for application flexibility.

### Applications:

Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with removable and hinged covers for application flexibility.

### Specifications:

- Compression-molded fiberglass construction
- Overlapping flat, solid-covers
- Cover fastens with screws
- Type 304 stainless steel piano hinges on hinged models
- Integral mounting brackets
- Enclosures protect equipment and operators from indirect electrical contact

### Finish:

Fiberglass material is RAL 7035 light-gray inside and out. Optional steel panels are painted white. Optional stainless steel, aluminum, conductive and composite panels are unpainted.

**Accessories:**

- H2OMIT™ Vent Drains, Type 4X
- HOL-SEALERS™ Non-Metallic Hole Seals
- Panels for Junction Boxes
- Swing-Out Panel Kit
- Terminal Block Kit Assembly for Junction Boxes Overview

**Notes:**

- A x B x C are internal dimensions.
- Purchase panels separately. Optional stainless steel, composite and aluminum panels are available for most sizes.

## Technical Data

---

### Flat Cover with Screws, Type 4X

<b>Catalog Number</b>	<a href="#">HJ1008HWLG</a>
<b>A in.</b>	9.71
<b>B in.</b>	7.21
<b>C in.</b>	4.3
<b>K in.</b>	1.67
<b>L in.</b>	11.25
<b>D in.</b>	5.15
<b>F in.</b>	4.88
<b>G in.</b>	10.75
<b>H in.</b>	6.00
<b>Panel Size in.</b>	8.75 x 6.88
<b>J in.</b>	4.28
<b>W in.</b>	9.25
<b>Q in.</b>	6.24
<b>P in.</b>	8.25
<b>Aluminum Panel</b>	A10P8AL
<b>Steel Panel</b>	A10P8
<b>I in.</b>	11.51
<b>Door Fasteners</b>	Hinged, 2 screws
<b>Material</b>	Fiberglass

## Certifications

---



EU Certification

## Documents

---



2D DXF CAD



3D STEP CAD



Spec Sheet



Dimension Drawing

No accessories available.