



Nothing but **HEAVY DUTY.**

CUTS LABOR COSTS IN HALF



2210-20

FLUORESCENT LAMP AND BALLAST TESTER





Nothing but **HEAVY DUTY.**

FLUORESCENT LAMP AND BALLAST TESTER CUTS LABOR COSTS IN HALF

INCREASE PRODUCTIVITY



- Diagnose lamp, ballast, and pin failures in seconds
- Detect if an electronic ballast is working properly without removing the lamps or ballast cover plate
- Test the working condition of fluorescent lamps before or after installing
- Small portable size fits in pockets, tool belts and most carry cases

EASY TO USE



- 2.5' retractable antenna for extended testing reach and portable carrying
- Built-in LED flashlight illuminates dark work spaces
- Visual and audible alerts for ballast and pin tests



Removable antenna adapter
improves lamp test response

2.5' fully retractable antenna
for extended reach when testing

Complete 3-in-1 solution – test lamps, ballasts and pins

Durable tool continues to work after 6.5 foot drop



Built-in LED work light
illuminates dark work spaces

Visual and audible indicators
provide easy feedback

Dial and buttons
positioned for one-handed use

Rugged over-molding
for increased durability and grip

SPECIFICATIONS

Lamp Size	All Ranges of Fluorescent Lamps (T2-T12)
Ballast Test	Detects Electronic Ballasts Only
Pin Test	All Bi-Pin Fluorescent Lamps
Antenna Length	2.5'
Certifications	UL, CE



2210-20 Kit Includes:
Fluorescent Lamp and Ballast Tester, Soft Carry Case, Antenna Adapter, Manual and (4) AA Batteries