




## RIGID BODIES AND ASSEMBLIES

### LL Assembly

C13



Catalog #: RLL200

#### APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.  
N/A

#### PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

#### UL LISTED

File E331564

#### NEMA

NEMA 3R rated

#### NEC

2014 NEC® compliant

#### GENERAL PRODUCT INFORMATION

Trade Size: 2 in.

#### DRAWING DIMENSIONS

- Dimension A: 10.05 in.
- Dimension B: 4.27 in.
- Dimension C: 3.41 in.
- Dimension D: 3.19 in.
- Dimension E: 8.562 in.
- Dimension F: Tapped holes #12-24UNC-2B
- Dimension G: 2-11 1/2NPT
- Dimension H: 2.057 in.

#### PRODUCT MEASUREMENTS

Cubic Inches (cm3): 67.0 (1098)

#### PACKAGING

- Package Type: Carton
- Ship Carton Qty.: 2
- Product UPC-A Labeled: Yes
- Weight (Lbs. Per/C): 215.00
- Ship Carton Length (in.): 11.13
- Ship Carton Width (in.): 4.75
- Ship Carton Height (in.): 8.00
- Ctn Weight (Lbs.): 4.30
- UPC Number: 092326213271
- I2of5: 30092326213272