




RIGID BODIES AND ASSEMBLIES

T Assembly

C13



Catalog #: RLT050

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.

DRAWING DIMENSIONS

- Dimension A: 4.72 in.
- Dimension B: 2.03 in.
- Dimension C: 1.36 in.
- Dimension D: 1.34 in.
- Dimension E: 3.500 in.
- Dimension F: Tapped holes #8-32UNC-2B
- Dimension G: 1/2-14NPT
- Dimension H: .612 in.

PRODUCT MEASUREMENTS

Cubic Inches (cm3): 4.3 (70.5)

PACKAGING

- Package Type: Carton
- Ship Carton Qty.: 5
- Product UPC-A Labeled: Yes
- Weight (Lbs. Per/C): 37.60
- Ship Carton Length (in.): 16.93
- Ship Carton Width (in.): 3.63
- Ship Carton Height (in.): 6.69
- Ctn Weight (Lbs.): 1.88
- UPC Number: 092326211994
- I2of5: 30092326211995