




RIGID BODIES AND ASSEMBLIES

Service Entrance Elbow

C13



| CATALOG NUMBER | CONDUIT SIZE | A | B | C |
|----------------|--------------|-------|-------|-------|
| RSLB50 | 1/2" | 1.587 | 1.366 | 3.25 |
| RSLB75 | 3/4" | 1.878 | 1.693 | 3.663 |
| RSLB100 | 1" | 2.087 | 1.917 | 4.272 |
| RSLB125 | 1-1/4" | 2.579 | 2.39 | 5.506 |
| RSLB150 | 1-1/2" | 2.997 | 2.654 | 6.217 |
| RSLB200 | 2" | 3.075 | 3.122 | 6.715 |



Catalog #: RSLB150

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1-1/2 in.

DRAWING DIMENSIONS

Dimension A: 2.697 in.
 Dimension B: 2.654 in.
 Dimension C: 6.217 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 2
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 85.00
 Ship Carton Length (in.): 6.38
 Ship Carton Width (in.): 3.50
 Ship Carton Height (in.): 7.13
 Ctn Weight (Lbs.): 1.70
 UPC Number: 092326212496
 I2of5: 30092326212497