




## RIGID BODIES AND ASSEMBLIES

### Service Entrance Elbow

C13



CATALOG NUMBER	CONDUIT SIZE	A	B	C
RSLB50	1/2"	1.587	1.266	3.25
RSLB75	3/4"	1.878	1.593	3.663
RSLB100	1"	2.087	1.917	4.272
RSLB125	1-1/4"	2.579	2.39	5.506
RSLB150	1-1/2"	2.997	2.654	6.217
RSLB200	2"	3.075	3.122	6.715



Catalog #: RSLB200

#### APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

N/A

#### PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

#### UL LISTED

File E331564

#### NEMA

NEMA 3R rated

#### NEC

2014 NEC® compliant

#### GENERAL PRODUCT INFORMATION

Trade Size: 2 in.

#### DRAWING DIMENSIONS

Dimension A: 3.075 in.  
 Dimension B: 3.122 in.  
 Dimension C: 6.715 in.

#### PACKAGING

Package Type: Carton  
 Ship Carton Qty.: 2  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 110.00  
 Ship Carton Length (in.): 6.75  
 Ship Carton Width (in.): 3.63  
 Ship Carton Height (in.): 7.25  
 Ctn Weight (Lbs.): 2.20  
 UPC Number: 092326212502  
 I2of5: 30092326212503