



## Thin-Wall Heat-Shrinkable Tubing

T&B Catalog Number:

CPO187-0-6

UPC Number:

78621085163

Status:

Active

Description:

Thin-Wall Heat-Shrinkable Tubing for Cable Range 22-14 AWG, Expanded Dia. 3/16, Length 6 in., rated for 600V, 125 degrees C, Material: Cross-linked polyolefin - Non-lined, Black

### Features

Flame-retardant, cross-linked polyolefin.

Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

### General

|                   |                                     |
|-------------------|-------------------------------------|
| Style             | CPO Series Non-Lined, 6 in. lengths |
| Color             | Black                               |
| Temperature Range | -55°C - 135°C                       |
| Shrink Ratio      | 2:1                                 |

### Dimension Information

|                                 |           |
|---------------------------------|-----------|
| Minimum Expanded I.D. (inches)  | 0.187     |
| Maximum Recovered I.D. (inches) | 0.093     |
| Nominal Recovered Wall (inches) | 0.02      |
| Cable Range                     | 22-14 AWG |
| Standard Length (inches)        | 6         |

### Specifications

|                    |       |
|--------------------|-------|
| Shrink Temperature | 120°C |
|--------------------|-------|

### Packaging

|                    |                    |
|--------------------|--------------------|
| T&B Order Multiple | 20                 |
| T&B Inner Pack     | 20                 |
| Package in Units   | 200                |
| T&B Sold in UOM    | Each               |
| T&B Weight Per UOM | 3.13 lbs. per 1000 |

### Application Support

|                |                      |
|----------------|----------------------|
| MSDS Number    | msds-0020-tb2        |
| Specifications | Available on Website |
| Overview       | Available on Website |

### Notes

Order multiple is standard package.

Custom colors available. Contact Customer Service.

### Certifications

|                 |     |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

### Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)