



Powering Business Worldwide

pe.eaton.com

1 in Type BR Solar Power Center Meter Breaker

MBE1224PV125BTF

UPC:786685690209

Dimensions:

- **Height:** 23.9 IN
- **Length:** 5.31 IN
- **Width:** 14.45 IN

Weight:30 LB

Warranties:

- 10 year

Specifications:

- **Special Features:** Side by side construction
- **Type:** BR solar-ready
- **Amperage Rating:** 125A
- **Bus Material:** Aluminum
- **Bus Rating:** 125 A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Galvanized steel
- **Feed Type:** Overhead/underground
- **Input:** 25 max PV input
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Flush mounting
- **Number Of Circuits:** 24
- **Number Of Sockets:** 1
- **Number Of Spaces:** 12
- **Phase:** Single-phase
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V
- **Box Size:** 2

Supporting documents:

- [Solar power centers](#)
- [Eatons Volume 15-Solar Inverters and Electrical](#)



Balance of System

- Eaton Specification Sheet -
MBE1224PV125BTF

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.