




4 IN. SQUARE WELDED BOXES - 1-1/2 IN. DEEP WITH ARMORED CABLE / METAL CLAD / FLEX CLAMPS

4 in. Square Box, 2-1/8 in. Deep - Welded with STAB-IT Connector
600V, Raised Ground, 8" #12 Solid Copper Pigtail, UBS, M Bracket

A18



Catalog #: 232MS

APPLICATIONS

RACO® STAB-IT boxes are great for any job where flexible armored cable is being used
RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles

PRODUCT FEATURES

Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
TKO® Knockouts offer greater flexibility with RACO patented combination 1/2" and 3/4" knockout
UBS Support - Welded to box, preset bend points to work with wall thickness 2-1/2" to 6"

UL LISTED

File E195978

CULUS

N/A

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com
MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Armored Cable/Metal Clad/MCI-A/Flex
Color: Gray
Country of Origin: USA

CONFIGURATION

Cable Priouts: 2
Bracket Type: M Bracket
Bracket Setback: 3/8 In.
Drawn or Welded: Welded
Raised Ground: Yes
Gangs: 2
Side Knockout(s): (6) 1/2", (3) 1/2"-3/4" TKO
Bottom Knockouts(s): (1) 1/2", (1) 1/2"-3/4" TKO

PRODUCT MEASUREMENTS

Depth: 2-1/8 In.
Cubic Inches (cm3): 30.3 (496.5)
Product Length (in.): 2.750
Product Width (in.): 5.860
Product Height (in.): 4.000

PACKAGING

Package Type: Boxed
Minimum Pack Qty.: 25
Std. Pkg.: 25
Ship Carton Qty.: 25
Product UPC-A Labeled: No
Ship Carton Length (in.): 20.875
Ship Carton Width (in.): 8.500
Ship Carton Height (in.): 9.000
Pallet Qty: 1375
UPC Number: 050169500736
I2of5: 50050169500731

