

5362-S1W

Tamper Resistant Receptacles



UPC Code: 07847771089

Country of Origin: Mexico - *Eligible for ARRA funded projects > \$7,443,000

NEMA: 5-20R



Brand Features

Leviton offers custom imprinting solutions to meet the 2014 National Electrical Code requirements for identifying receptacles that will be automatically de-energized as part of an overall plug load control program. All 15A & 20A, 125V receptacles that are automatically controlled will be marked with a specific symbol.

Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Industrial Series Extra Heavy Duty Specification Grade, Duplex Receptacle, Hot Terminal Split w/1 Plug Controlled, Straight Blade, Self Grounding, Back & Side 8 Hole Feed-Thru Wired, Contractor Pack - WHITE

Technical Information

AC Horsepower Ratings
At Rated Voltage: 1 HP

Electrical Specifications

Amperage: 20 Amp
Voltage: 125 Volt
NEMA: 5-20R
Grounding: Self-Grounding
Pole: 2
Wire: 3

Dielectric Voltage: Withstands 2000V per UL498
Temperature Rise: Max 30C after 250 cycles OL at 200 percent rated current

Environmental Specifications

Flammability: Rated V-2 per UL94
Operating Temperature: -40°C to 75°C

Material Specifications

Face Material: Nylon
Body Material: Nylon
Line Contacts: Triple-Wipe .040" High Performance Brass Alloy
Terminal Clamp: Zinc-Plated Steel
Terminal Screws: Brass 10-32
Grounding Screw: Brass 8-32
Strap Material: Brass .050"
Ground Clips: Brass

Mechanical Specifications

Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral
Terminal Accom.: 14-10 AWG
Wire Type: Solid or Stranded Building Wire
Product ID: Ratings are permanently marked on device
Termination: Back & side wiring, 8 back-wiring holes

Product Features

Color: White
NEMA: 5-20R

Standards and Certifications

NEMA: WD-1 & WD-6
ANSI: C-73
Certification/Listing: UL, CSA, NOM-ANCE
Applicable Standards: UL 498, CSA C22.2 No. 42, FedSpec W-C 596

Warranty

Warranty: 10-Year Limited

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012-2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.



Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

**Buy American Compliant Logo -- The American Recovery And Reinvestment Act of 2009 ("ARRA") provides federal grants and loans for projects throughout the country. Section 1605 of the Act, named the "Buy American" provision, requires that certain materials and manufactured products used in projects funded by the Act be manufactured in the United States. The appearance of the Recovery Act Logo in relation to a Leviton product is only intended to reflect that such product may be used in an ARRA funded project. It does not mean that such product or Leviton is sponsored or endorsed by, or that Leviton receives funds from, the federal government or the Recovery Accountability and Transparency Board. Nothing in Leviton's use of the logo is intended to suggest anything regarding the requirements for funding under ARRA.*