



Family

**Catalog Number:** 132-W-FB-1/2  
**Product ID:** 7TAA001600R0003  
**UPC Number:** 78172004304  
**Status:** Active

Two Gang Device Box, 30.3 Cubic Inches, 4 Inch Square x 2-1/8 Inch Deep, 1/2 Inch Knock-outs, Galvanized Steel, Welded Construction, with Flat Bracket Offset 9/16 Inch from Face, For Use with Conduit

### North American Specifications (UNSPSC)

UNSPSC	39121306 Switch box
IGCC	4430 Switch box
Brand Name	Steel City
Type	Gang Boxes
Application	For use with Conduit
Standard	UL E2969
Material	Steel
Size	4 Inches Length x 4 Inches Width x 2-1/8 Inches Depth
Color	Silver
Construction	Welded
Cubic Capacity	30.3 Cubic Inches
Knockouts	Yes
Number Of Outlet	2

### European Specifications (ETIM)

ETIM	EC002600 Box/housing for surface mounting on the wall/ceiling
Shape	Square
Mounting method	Wall-/ceiling mounting
Length	101.6mm
Width	101.6mm
Depth	53.975mm
Material	Steel
Weatherproof	N

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	24.25x10.25x8
Weight Uom	92 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)