

Control Power Transformer, 300va, PRI 240x480 230x460 220 440v,
SEC 120/115/110v, Domestic,



Figure similar

Product brand name	Control Power Transformer
Product designation	MT
Special product feature	Robust design

General technical data

Weight [lb]	11.3 lb
Height x Width x Depth [in]	4.47 × 4.5 × 4.87 in
Ambient temperature [°F] during operation	-4 ... +104 °F
Ambient temperature during operation	-20 ... +40 °C
Country of origin	Mexico
Operating apparent output rated value	300 V·A

Enclosure

Design of the housing	Open
-----------------------	------

Mounting/wiring

Mounting position	Any
Mounting type	Surface mounting
Type of electrical connection at output for main current circuit	Screw-type terminals (touchsafe)

Type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)
---	----------------------------------

Inputs/ Outputs

Input dimensions of primary voltage	240x480,230x460,220x440vac
Output dimensions of secondary voltage	120/115/110vac
Phase number of the inputs	1
Electrical input frequency	50 ... 60 Hz
Input voltage _1	240 V
Input voltage _2	480 V
Input voltage _3	230 V
Input voltage _4	460 V
Input voltage _5	220 V
Input voltage _6	440 V
Phase number of the outputs	1
Electrical output frequency	60 ... 50 Hz
Output voltage _1 rated value	120 V
Output voltage _3 rated value	110 V
Output voltage _2 rated value	115 V

Certificates/approvals

Certificate of suitability	UL / CSA
----------------------------	----------

Further information

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT0300A>

last modified: 08/07/2017