

4U Series 12V Xenon Collection 12" Xenon Harmonization 12V Cabinet Light - BZT

4U12X12BZT (Bronze Textured)



Dimensions

Height	1.25"
Length	12.00"
Width	4.50"

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	4U12X12BZT
Finish	Bronze Textured
Available Finishes	BZT, NIT, WHT
Collection	4U Series 12V Xenon Collection

Dimensions

Weight	1.40 LBS
--------	----------

Specifications

Material	Aluminum
Diffuser Description	Frosted

Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)
Operating Voltage Range	108-132V
Switch Type	Hi-Low-Off, Rocker

Qualifications

Safety Rated	Dry
Expected Life Span	10000 Hours
Warranty	www.kichler.com/warranty

Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	0.5 in
Number of Knockouts	5
Modular	Yes

Primary Lamping

Light Source	Incandescent
Lamp Included	Included
# of Bulbs/LED Modules	2
Max or Nominal Watt	18W
Socket Type	Wedge T5
Bulb Product ID	10574CLR
Dimming	Yes

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.